

X Ultra Set

Intelligent & Scientific Oral Care Mentor For the Ultra Clean & Focused Sensory **Brushing Experience**

improve Gum Health 84,000 movements / min **Motor Movements**

Helps remove more plaque and

Max.Torque (gf.cm)

260 gf.cm

Swing Angle

Up to 11° > 5000 hours

Lifetime

Cleaning Performance

🔵 Ultra Clean *1 Reduce 40% More Plaque* Innovative 5° Design - Deep

Ultra White *1

Clean below the Gum Line

FlexFit Tech - the Best Interdental Clean & Teeth Protection

+20% Resilience Bristles* -Special Design for Exceptional Cleaning Efficiency

Reduce 38% More Stains*

Innovative 5° Design - Deep Clean below the Gum Line

Ultra Gum Care *1

FlexFit Tech - the Best Interdental Clean & Teeth

Protection

Polishing Rubber Ring - Gently Removes Surface Stains to Whiten Teeth

Contact & Gentle Cleaning

Gentle for Sensitive Gums +20% Density* - More Surface

Protection +20% Softer Bristles* - Special

Interdental Clean & Teeth

Design for Protecting Gum

FlexFit Tech - the Best

and Enamel

Sunset Clearout,

Method etc.)

Sensitive Gum Care,

Whitening Polishing

Unlimited Clean (5 Power Level to adjustment), Sunrise Soothing,

App Customized brush mode (Meditation SPA, Yoga

Whitening, Scientific Brush

Brush Mode

5 + N Customized

Unlimited Clean Soothing Clearout Sensitive Quen Care Polishing



Intensity Levels: 32 Level (Customize on APP) Duration Adjustment: Up to 5 mins (Customize on APP)

Linear Pressure Sensing Precise linear pressuresensitive gingival protection and transitional horizontal

> Constant amplitude, constant force, super clean power

pull reminder

Oclean Turbo GT

Algorithm

Brushing algorithm

power compensation Default parameter learning algorithm, software-defined hardware

Real-time power and electric quantity monitoring, real-time

Supported

calculated

Helps to infinite control your smart electric toothbrush

Effective brushing time is

Timer 2 min

Quad Pacer 30 secs **Interactive Feedback** Dental Mold in OLED Screen

Brushing Time display

Smart Brush Feature

Auto-Wake

OLED Touch Screen

16 Languages,

select model

Slide up or down to

5 Level on Screen

Single brushing time,

White: clean the area

Orange: Unclean area

Tooth brushing score to judge the overall situation

Brush your teeth twice a day

The average score of tooth

Get through Apple Weather

Kit and global clock

<45dB (Defalt),

othe mode < 55dB

of tooth brushing

Adaptive to APP Language

Vertical Slide

Global UI

Horizontal Slide Horizontal sliding for more Information Display

Brush Report

force

Multi-gear

adjustable

Oral Care Fresh Clover

brushing > 90 CRing 3: average effective brushing time > 2min

Ring 1:

Ring 2:

Operation Nosie Oclean Exclusive WisperCare Technology

Certification

Other Feature

CNAS

Over Pressure rimander

Make the value of color

touch screen explicit in the

Anti-splash power reduce

Retailer Counter Display Mode

Other Feature

Pressure Detection

everyday

retail terminal

Oral Care Fresh Clover

Featival Greetings Motor sound feedback

during forward

operation

Light Show

Different sound feedback in different scenes will bring more surprises to users. Like the ring of "Oclean"

Achieve all indicators on the

same day and trigger the


celebration egg (fireworks + light show)

temperatuure


(·)) Over Pressure

Let technology have

With the trigger scene of the motor sound effect, the WiFi



feel the ritual of brushing their teeth




Helps to have good brush habit

•**))** Brushing Too Fast (.)

lamp, Logo lamp and base lamp of the toothbrush are lit up in turn to form a simple

light show, which makes users



to know whether it is working and whether charging is complete during charging. *Compatiable with Apple

and add a charging indicator light to avoid being unable

Type C to Type C cable.

wireless charging,

Helps display better and anti-mold Waterproof IPX7 Hydrophobic antibacterial PPG second generation touch UV paint Anti-dirt Scratch Resistance Newly Design Wallmount **Travel Care with** Upgrade the product in the **Charging Port** XPD travel box, change to

Oclean Bone Conduction Brush Over Pressure Reminder **Al Voice Guidance** Brush excessive horizontal

Helps not miss a blind zone and brush behavior scientifically

30s brush zone change

pulling Reminder

2 mins timing smart voice reminder 45 ° inclined brush reminder

Brush the occlusal surface reminder

Oclean Gesture Tracking Algorithm

OLED Color Screen

Oral Care Fresh Clover

Oclean Blind Detection

Visualized Brushing

Algorithm

Data

App

Brush Report

Device Control

Oral Care Content

Charging &

Low battery alert

Charging Port

Charging Time

Charging Time

Battery

Battery Type

Care Plan

Brushing Time

Brushing Score

BlindZone Display

Brushing Progress Animation &

Brush your teeth twice a day

Ring 2: The average score of tooth brushing > 90

Ring 3:

Daily, Weekly,

average effective brushing time > 2min

Device Status, Voice, Brush Program, Brush Head Replace Reminder etc Recommended Professional

Oral Care Schemes

Monthly Report Analyse

(Upgrade Later) Orthodontic According to the orthodontic record, the mode and **Punch Card**

> (Upgrade Later) Oral Health Knowledge, Join brush meditation community and Yoga white community

scheme are automatically

pushed in different periods

(orthodontic adaptation period, retainer period, retainer period)

More precise and

Wirless Charge

4.5-hour quick charge

friendly reminders by OLED screen

(Upgrade Later)

Helps charge safely , quickly , not so

frequently and charging everywhere

Charging Box Charging Port

Charging Station

Apple Type C to Type C cable) 8-hour quick charge

Type C (Compatible with

Apple iPhone 15 and

Built-in Li-Ion 3.7V

1200 mAh

5V === 1A

Battery Capacity Charging Input

Operational Time

40 Days

(★Bluetooth)+(ŞWi-Fi)

Matter (OTA Upgrade later)

to ensure the best oral care

Compatible with Android 4.4, IOS 8.0 and above with Bluetooth 4.0 support

Update version by version

Apple Weather provides a global weather forecast

LAN Self-discovery, Homekit,

Alexa, Google Home control,

Apple Research Kit & Care Kit:

Digitally Empowering Oral

Oclean Care + 3.4

Smart Connectivity

Connectivity

Connect Method

Buletooth Version

Wi-Fi Frequnce

Special Protocal

Range

OTA Upgrade Remotely upgrade the toothbrush to keep the latest functions and technologies

Processing Capability* **Control Unit**

CPU Frequency

Memory Capacity

Operating System

Goodix 5515x ARM cortex M4F 4*4 MB

Oclean OS

2.4G

5 - 10m

Sensors 6-axis gyroscope, Liner Pressure Sensor, Bone Conduction Monitor etc

Oclean Care + App **Platform**

IoT Platform

Oclean Care + Version

More Feature to

Apple Ecosystem

Explore

service Apple Health: Apple Health Integrated Oclean Toothbrushing Report

Interoperability Skills (OTA Upgrade Later)

Care Researchers

brushing report

Weather Kit:

Apple Matter:

Huawei Hilink & Hihealth

What's in the box

Smart IOS/Android Push, watchOS, Widgets, and a lot of IoT functions (OTA Upgrade Later) WeChat IoT gets through, automatically push tooth

Huawei HiLink and Hihealth

have become an important data dimension of Huawei

Watch GT's health strategy.

(OTA Upgrade Later)

Packaging List

Packaging Language

UI/Vioce List

ESG

Ultral Cleanl Brush Head* 1; Ultral Gum Care Brush Head *1; Ultral Whitening Brush Head*1; Type C Travel Case *1; Wireless Charger*1; Wall Mount*1

Package Front:

Package Back USPs:

EN/FR/DE/IT/ES/PL/RU

Toothbrush Body * 1;

32 Languages User Manul*1;

German, Russian, Polish, Italian,

ΕN

QIG * 1;

16 Languages, Adaptive to APP Language; Chinese, Chinese(Traditional), English, Japanese ,Korean ,

Portuguese (Brazilian), French, Spanish, Turkish, Ukrainian, Czech ,Hebrew ,Arabic

🐴 All Paper Packaging

Environmental-Friendly

The product pictures shown are for reference only. Please refer to the actual product for details and configurations.

All data is based on our technical design parameters, laboratory test results and supplier test data. Actual performance may vary depending on software version, specific test environment and phone model